

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300910018](#)
Status: **Active**
Overview: [Reels - Woodhead](#)
Description: Woodhead Standard Cord Reel, 16/3 SJTOW Cord, 15.24m (50.0') Cord Length with 15A Connector, NEMA 5-15

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
UL	E22769
General	
Product Family	Electric Reels
Series	130091
Cable Length	0.457m (1.50')
Depth	0.30m (11.75")
Duty	Standard
Enclosure Rating	NEMA 1
Height	0.36m (14.25")
NEMA Configuration	NEMA 5-15
Overview	Reels - Woodhead
Product Name	Super-Safeway
Type	Cord Reel
UPC	78678833617
Width	196.85mm (7.750")
Physical	
Cable Movement	Ratchet Lock
Cord Length	15.24m (50.0')
Drum Lock	Ratchet
Guide Arm	2 - Position
Material - Coating	Powder Coating
Material - Housing	Steel/Polycarbonate
Mounting Style	Rigid
Number of Conductors	3
Number of Receptacles	1
Packaging Type	Carton
Primary Cord/Cable Entry	N/A
Retraction Weight	1.4kg (3.0 lb)
Wire Size AWG	16
Electrical	
Bulb Included	N/A
Cord Type	16/3 SJTOW
Current - Maximum per Contact	8.0A
GFCI	No
Lamp Type	N/A
Lamp Wattage - Maximum	N/A
On/Off Switch	No
Voltage - Maximum	120V
Material Info	
Engineering Number	980-1547



EU ELV Not Relevant	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130091](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300910018