

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1300910020](#)  
**Status:** **Active**  
**Overview:** [Reels - Woodhead](#)  
**Description:** Woodhead Standard Duty Reel, 16/3 SJTOW Cord, 15.24m (50.0') Cord Length with 30W Maximum Low Volt Incandescent Spot Light

**Documents:**  
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

|                               |                                  |
|-------------------------------|----------------------------------|
| <b>General</b>                |                                  |
| Product Family                | Electric Reels                   |
| Series                        | <a href="#">130091</a>           |
| Cable Length                  | 0.457m (1.50')                   |
| Depth                         | 0.30m (11.75")                   |
| Duty                          | Standard                         |
| Enclosure Rating              | NEMA 1                           |
| Height                        | 0.36m (14.25")                   |
| NEMA Configuration            | NEMA 5-15                        |
| Overview                      | <a href="#">Reels - Woodhead</a> |
| Product Name                  | Super-Safeway                    |
| Type                          | Cord Reel                        |
| UPC                           | 78678833614                      |
| Width                         | 196.85mm (7.750")                |
| <b>Physical</b>               |                                  |
| Cable Movement                | Ratchet Lock                     |
| Cord Length                   | 15.24m (50.0')                   |
| Drum Lock                     | Ratchet                          |
| Guide Arm                     | 2 - Position                     |
| Material - Coating            | Powder Coating                   |
| Material - Housing            | Steel/Polycarbonate              |
| Mounting Style                | Rigid                            |
| Number of Conductors          | 3                                |
| Packaging Type                | Carton                           |
| Primary Cord/Cable Entry      | N/A                              |
| Retraction Weight             | 1.4kg (3.0 lb)                   |
| Wire Size AWG                 | 16                               |
| <b>Electrical</b>             |                                  |
| Bulb Included                 | Yes                              |
| Cord Type                     | 16/3 SJTOW                       |
| Current - Maximum per Contact | 8.0A                             |
| GFCI                          | No                               |
| Lamp Type                     | Incandescent                     |
| Lamp Wattage - Maximum        | 30W                              |
| On/Off Switch                 | Yes                              |
| Transformer Type              | Reel Mounted                     |
| Voltage - Maximum             | 120V                             |
| <b>Material Info</b>          |                                  |
| Engineering Number            | 980-1610S                        |



Series image - Reference only

|                                                               |                   |
|---------------------------------------------------------------|-------------------|
| <b>EU ELV</b><br><b>Not Reviewed</b>                          |                   |
| <b>EU RoHS</b><br><b>Not Reviewed</b>                         | <b>China RoHS</b> |
| <b>REACH SVHC</b><br>Not Reviewed                             |                   |
| <b>Halogen-Free</b><br><b>Status</b><br><b>Not Reviewed</b>   |                   |
| For more information, please visit <a href="#">Contact US</a> |                   |
| China ROHS                                                    | Not Reviewed      |
| ELV                                                           | Not Reviewed      |
| RoHS Phthalates                                               | Not Reviewed      |

**Search Parts in this Series**  
[130091](#) Series

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300910020