

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300910028](#)
Status: **Active**
Overview: [Reels - Woodhead](#)
Description: Woodhead Standard Duty Reel, 16/3 SJTOW Cord, 15.24m (50.0') Cord Length with 13W Fluorescent Hand Lamp and Handle Ballast

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR29921
UL E22769

General

Product Family Electric Reels
Series [130091](#)
Cable Length 0.457m (1.50')
Depth 0.30m (11.75")
Duty Standard
Enclosure Rating NEMA 1
Height 0.36m (14.25")
NEMA Configuration NEMA 5-15
Overview [Reels - Woodhead](#)
Product Name Super-Safeway
Type Cord Reel
UPC 78678833610
Width 196.85mm (7.750")

Physical

Cable Movement Ratchet Lock
Cord Length 15.24m (50.0')
Drum Lock Ratchet
Guide Arm 2 - Position
Material - Coating Powder Coating
Material - Housing Steel/Polycarbonate
Mounting Style Rigid
Number of Conductors 3
Packaging Type Carton
Primary Cord/Cable Entry N/A
Retraction Weight 1.4kg (3.0 lb)
Wire Size AWG 16

Electrical

Bulb Included Yes
Cord Type 16/3 SJTOW
Current - Maximum per Contact 8.0A
GFCI No
Lamp Type Fluorescent
Lamp Wattage - Maximum 13W
On/Off Switch Yes
Voltage - Maximum 120V

Material Info

Engineering Number 980-86



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130091](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300910028