

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300910087

Status:

Active

Overview:

Reels - Woodhead

Description:

Woodhead Standard Cord Reel, 12/3 SJTOW Cord, 10.67m (35.0') Cord Length with 15A Connector, NEMA 5-15



Documents:

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR29921
UL	E22769
General	
Product Family	Electric Reels
Series	130091
Cable Length	0.457m (1.50')
Depth	0.30m (11.75")
Duty	Standard
Enclosure Rating	NEMA 1
Height	0.36m (14.25")
NEMA Configuration	NEMA 5-15
Overview	Reels - Woodhead
Product Name	Super-Safeway
Type	Cord Reel
UPC	78678838240
Width	196.85mm (7.750")
Physical	
Cable Movement	Ratchet Lock
Cord Length	10.67m (35.0')
Drum Lock	Ratchet
Guide Arm	2 - Position
Material - Coating	Powder Coating
Material - Housing	Steel/Polycarbonate
Mounting Style	Rigid
Net Weight	10886.208/g
Number of Conductors	3
Number of Receptacles	1
Packaging Type	Carton
Primary Cord/Cable Entry	N/A
Retraction Weight	1.4kg (3.0 lb)
Wire Size AWG	12
Electrical	
Bulb Included	N/A
Cord Type	12/3 SJTOW
Current - Maximum per Contact	15.0A
GFCI	No
Lamp Type	N/A
Lamp Wattage - Maximum	N/A
On/Off Switch	No
Voltage - Maximum	120V
Material Info	
Engineering Number	997-1547

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130091 Series

This document was generated on 07/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1300910087](#)