

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300910208

Status:

Active

Overview:

Reels - Woodhead

Description:

Woodhead Standard Duty Cord Reel, 12/3 SJTOW Cord, 10.67m (35.0') Cord Length, NEMA L5-20 Locking Plug, with 20A Single NEMA 5-20 Straight Blade Connector

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

Agency Certification	
CSA	LR29921
General	
Product Family	Electric Reels
Series	130091
Cable Length	0.61m (2.0')
Depth	0.30m (11.75")
Duty	Standard
Enclosure Rating	NEMA 1
Height	0.36m (14.25")
NEMA Configuration	NEMA L5-20
Overview	Reels - Woodhead
Product Name	Super-Safeway
Type	Cord Reel
UPC	78172548624
Width	196.85mm (7.750")
Physical	
Cable Movement	Ratchet Lock
Cord Length	10.67m (35.0')
Drum Lock	Ratchet
Guide Arm	2 - Position
Material - Coating	Powder Coating
Material - Housing	Steel/Polycarbonate
Mounting Style	Rigid
Number of Conductors	3
Number of Receptacles	1
Packaging Type	Carton
Primary Cord/Cable Entry	N/A
Retraction Weight	1.4kg (3.0 lb)
Wire Size AWG	12
Electrical	
Bulb Included	N/A
Cord Type	12/3 SJTOW
Current - Maximum per Contact	20.0A
GFCI	No
Lamp Type	N/A
Lamp Wattage - Maximum	N/A
On/Off Switch	No
Voltage - Maximum	120V
Material Info	
Engineering Number	998L-1533
Reference - Drawing Numbers	
Sales Drawing	SD-130091-018



EU ELV

Not Reviewed

EU RoHS

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130091 Series

This document was generated on 07/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300910208](#)