

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300910211](#)
Status: **Active**
Overview: [Reels - Woodhead](#)
Description: Woodhead Standard Duty Cord Reel, 12/3 SJTOW Cord, 10.67m (35.0') Cord Length, NEMA L5-15 Locking Plug, with 15A Single NEMA L5-15 Locking Connector

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

Agency Certification

CSA LR29921

General

Product Family Electric Reels
Series [130091](#)
Cable Length 0.61m (2.0')
Depth 0.30m (11.75")
Duty Standard
Enclosure Rating NEMA 1
Height 0.36m (14.25")
NEMA Configuration NEMA L5-15
Overview [Reels - Woodhead](#)
Product Name Super-Safeway
Type Cord Reel
UPC 78172548627
Width 196.85mm (7.750")

Physical

Cable Movement Ratchet Lock
Cord Length 10.67m (35.0')
Drum Lock Ratchet
Guide Arm 2 - Position
Material - Coating Powder Coating
Material - Housing Steel/Polycarbonate
Mounting Style Rigid
Number of Conductors 3
Number of Receptacles 1
Packaging Type Carton
Primary Cord/Cable Entry N/A
Retraction Weight 1.4kg (3.0 lb)
Wire Size AWG 12

Electrical

Bulb Included N/A
Cord Type 12/3 SJTOW
Current - Maximum per Contact 15.0A
GFCI No
Lamp Type N/A
Lamp Wattage - Maximum N/A
On/Off Switch No
Voltage - Maximum 120V

Material Info

Engineering Number 997L-2547

Reference - Drawing Numbers

Sales Drawing SD-130091-021



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130091](#) Series

This document was generated on 07/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1300910211](#)