

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300920038

Status:

Active

Overview:

Slip Rings

Description:

Aero-Motive Enclosed Slip Ring, 30A, 10 AWG, 11 Conductors

Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR19099
UL		E110371
General		
Product Family		Slip Rings
Series		130092
Center Bore Diameter		N/A
Component Type		Enclosed
Current - Maximum per Contact		30.0A
Mounting Style		Vertical
Number of Conductors		11
Overview		Slip Rings
Packaging Type		Carton
Product Name		Aero-Motive
Speed (RPM)		Continuous 10
Temperature Range - Operating		-40°C to +120°C
UPC		78678867697
Voltage - Maximum		600V
Wire Size AWG		10
Material Info		
Engineering Number		ISRC311



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130092 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300920038