

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300920098

Status:

Active

Overview:

Slip Rings


Description:

Aero-Motive Self-Contained Slip Ring, 30A, 12 AWG, 3 Conductors, Bore Size 22.23mm (.875") Diameter

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Slip Rings
Series	130092
Center Bore Diameter	22.23mm (.875")
Component Type	Self-Contained
Current - Maximum per Contact	30.0A
Mounting Style	Horizontal, Vertical
Number of Conductors	3
Overview	Slip Rings
Packaging Type	Carton
Product Name	Aero-Motive
Speed (RPM)	Continuous 125
Temperature Range - Operating	-40°C to +120°C
UPC	78678859301
Voltage - Maximum	600V
Wire Size AWG	12
Material Info	
Engineering Number	SR203



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130092 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300920098](#)