

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300920106](#)
Status: **Active**
Overview: [Slip Rings](#)
Description: Aero-Motive Slip Ring Component Kit, 30A, 12 AWG, 2 Conductors, Bore Size 22.23mm (.875") Diameter

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Slip Rings
Series	130092
Center Bore Diameter	22.23mm (.875")
Component Type	Component Kit
Current - Maximum per Contact	30.0A
Mounting Style	Horizontal, Vertical
Number of Conductors	2
Overview	Slip Rings
Packaging Type	Carton
Product Name	Aero-Motive
Speed (RPM)	Continuous 125
Temperature Range - Operating	-40°C to +120°C
UPC	78678859309
Voltage - Maximum	600V
Wire Size AWG	12
Material Info	
Engineering Number	SR22



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130092](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300920106