

6

5

4


3

2

1

CATALOG NUMBER	MATERIAL NUMBER	CABLE RANGE	LENGTH "M"	LENGTH "B"	ROD LENGTH	ROD DIAMETER REF.	APPROXIMATE BREAK STRENGTH* (LBS/N)	SHOULDER PROTECTOR	UL LISTED	CSA APPROVED	PRODUCT SELECTION NUMBER
35270SS	1300941643	.50-.61 / 12.7-15.5	11.0±1.0 / 279±25	7.0±1.0 / 178±25	15.0±0.5 / 381±13	.093 / 2.36	770 / 3425	YES	NO	NO	SR050-UU
35271SS	1300940369	.62-.74 / 15.7-18.8	11.0±1.0 / 279±25	7.0±1.0 / 178±25	15.0±0.5 / 381±13	.093 / 2.36	1150 / 5115				SR062-UU
35272SS	1300940371	.75-.99 / 19.1-25.1	14.0±1.0 / 356±25	7.0±1.0 / 178±25	18.0±0.5 / 457±13	.093 / 2.36	1320 / 5872				SR075-UU
35273SS	1300940373	1.00-1.24 / 25.4-31.5	15.0±1.5 / 381±38	7.0±1.0 / 178±25	19.0±0.5 / 483±13	.093 / 2.36	1920 / 8541				SR100-UU
35274SS	1300940375	1.25-1.49 / 31.8-37.8	16.0±1.5 / 406±38	7.0±1.0 / 178±25	21.0±1.0 / 533±25	.125 / 3.18	1920 / 8541				SR125-UU
35275SS	1300940377	1.50-1.74 / 38.1-44.2	18.0±1.5 / 457±38	7.0±1.0 / 178±25	23.0±1.0 / 584±25	.125 / 3.18	1920 / 8541				SR150-UU
35276SS	1300940379	1.75-1.99 / 44.5-50.5	20.0±1.5 / 508±38	7.0±1.0 / 178±25	25.0±1.0 / 635±25	.125 / 3.18	3150 / 14012				SR175-UU
35277SS	1300940381	2.00-2.49 / 50.8-63.2	22.0±2.0 / 559±51	7.0±1.0 / 178±25	27.0±1.0 / 686±25	.156 / 3.96	3360 / 14946				SR200-UU
35278SS	1300941642	2.50-2.99 / 63.5-75.9	24.0±2.0 / 610±51	7.0±1.0 / 178±25	30.0±1.0 / 762±25	.156 / 3.96	3360 / 14946				SR250-UU
35279SS	1300940006	3.00-3.49 / 76.2-88.6	26.0±2.0 / 660±51	9.0±1.0 / 229±25	32.0±1.0 / 813±25	.156 / 3.96	7520 / 33451	NO			SR300-UU
35280SS	1300940007	3.50-3.99 / 88.9-101.3	28.0±2.0 / 711±51	9.0±1.0 / 229±25	34.0±1.0 / 864±25	.156 / 3.96	7520 / 33451				SR350-UU

* TO DETERMINE RECOMMENDED WORKING LOAD, DIVIDE BREAK STRENGTH BY 10.



VIEW SHOWN WITH SHOULDER PROTECTOR

ITEM	DESCRIPTION	MATERIAL
1	SHOULDER PROTECTOR	STAINLESS STEEL
2	BALE WIRE	STAINLESS STEEL
3	FERRULE	STAINLESS STEEL
4	CRIMP CONNECTOR	STAINLESS STEEL
5	WIRE MESH	STAINLESS STEEL
6	ROD	STAINLESS STEEL
7	LABEL	MYLAR

ADDED 1300941642 & 1643	4/22/16
EC NO: IGC2016-1441	DRWN: HRUIZ01
CHKD: HRUIZ01	2016/04/22
APPR: JFMURPHY	2015/10/28
REV	
B	

QUALITY SYMBOLS
0=
0=

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±.005
2 PLACES	±.13	±.010
1 PLACE	±.25	±.020
ANGULAR ±1/2°		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE INCH/MM	
DRAWN BY	DATE
KCOX01	2015/08/03
CHECKED BY	DATE
HRUIZ01	2015/08/03
APPROVED BY	DATE
JFMURPHY	2015/10/28
MATERIAL NO.	
SEE TABLE	
SIZE	
A	

SCALE NTS	DESIGN UNITS INCH		THIRD ANGLE PROJECTION
TITLE			
SUPPORT GRIPS SST STANDARD DUTY DOUBLE EYE SPLIT ROD			
MOLEX INCORPORATED			
DOCUMENT NO.		SHEET NO.	
SD-130094-044		1 OF 1	
CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300940006