

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1300940233

Status: **Active**

Overview: Support Grips

Description: Standard Duty Support Grip, Single Eye, Closed Mesh, Single Weave, Cable Diameter 15.88-19.05mm (.625-.750"), Approximate Break Strength 435.45kg (960 lbs), Stainless Steel

Documents:

[Packaging Specification PK-130227-004-001 \(PDF\)](#)

RoHS Certificate of Compliance (PDF)

General

Product Family	Cable Grips
Series	<u>130094</u>
Eye Type	Single
NEMA Rating	NEMA 4
O-Ring	No
Overview	<u>Support Grips</u>
Product Name	Standard Duty
Type	Support Grip
UPC	78678809770

Physical

Approximate Break Strength	435.45kg (960 lbs)
Bale Length	0.203m (8.00")
Body Style	Straight
Cable Diameter	15.88-19.05mm (.625-.750")
Color - Grommet	N/A
Gender	N/A
Material - Body	N/A
Material - Grip	Stainless Steel
Mesh Length	0.279m (11.00")
Net Weight	589.000/g
Number of Holes	N/A
Thread Size	N/A

Material Info

Engineering Number 35031SS

Reference - Drawing Numbers

Packaging Specification PK-130227-004-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

130094 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300940233