

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300940265

Status:

Active

Overview:

Support Grips

Description:

Standard Duty Support Grip, Offset Eye, Closed Mesh, Single Weave, Cable Diameter 50.80-63.25mm (2.000-2.490"), Approximate Break Strength 1705.51kg (3760 lbs)

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR32159

General

Product Family

Series

Eye Type

O-Ring

Overview

Product Name

Type

UPC

Cable Grips

130094

Offset

N/A

Support Grips

Standard Duty

Support Grip

78678835067

Physical

Approximate Break Strength

Bale Length

Body Style

Cable Diameter

Color - Grommet

Gender

Material - Body

Material - Grip

Mesh Length

Number of Holes

Thread Size

1705.51kg (3760 lbs)

0.152m (6.00")

Straight

50.80-63.25mm (2.000-2.490")

N/A

N/A

N/A

Non-magnetic Tin Bronze Wire

0.559m (22.00")

N/A

N/A

Material Info

Engineering Number

35067



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130094 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300940265