

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300940328

Status:

Active

Overview:

Support Grips

Description:

Standard Duty Support Grip, Single Eye, Split Lace, Single Weave, Cable Diameter 76.20-88.65mm (3.000-3.490"), Approximate Break Strength 2286.11kg (5040 lbs)

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR32159

General

Product Family

Series

Eye Type

O-Ring

Overview

Product Name

Type

UPC

Cable Grips

130094

Single

N/A

Support Grips

Standard Duty

Support Grip

78678835174

Physical

Approximate Break Strength

Bale Length

Body Style

Cable Diameter

Color - Grommet

Gender

Material - Body

Material - Grip

Mesh Length

Number of Holes

Thread Size

2286.11kg (5040 lbs)

0.533m (21.00")

Straight

76.20-88.65mm (3.000-3.490")

N/A

N/A

N/A

Non-magnetic Tin Bronze Wire

0.66m (26.00")

N/A

N/A

Material Info

Engineering Number

35174



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130094 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

130094-0328