

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300960049

Status:

Active

Overview:

Strain-Relief Cord Grips

Description:

Liquid-Tight Grip Strain Relief, 2" NPT, 45° Angle Male, Mesh Length 0.19m (7.50")



Series image - Reference only

Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Brochure \(PDF\)](#)

Agency Certification	
CSA	LR32159
UL	E61303
General	
Product Family	Cable Grips
Series	130096
Eye Type	N/A
NEMA Rating	NEMA 4
O-Ring	N/A
Overview	Strain-Relief Cord Grips
Product Name	Liquid-Tight
Type	Strain Relief Grip
UPC	78678836395
Physical	
Approximate Break Strength	N/A
Bale Length	N/A
Body Style	45° Angle
Cable Diameter	N/A
Color - Grommet	N/A
Gender	Male
Material - Body	Malleable Iron, Zinc Plated Steel
Material - Grip	Stainless Steel
Mesh Length	0.19m (7.50")
Number of Holes	N/A
Thread Size	2" NPT
Material Info	
Engineering Number	36395
Reference - Drawing Numbers	
Sales Drawing	SD-130096-102

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130096 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300960049](#)