

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300960079](#)
Status: **Active**
Overview: [Strain-Relief Cord Grips](#)
Description: Liquid-Tight Grip Strain Relief for Non-Metallic Type A Flexible Conduit, 2" NPT, Straight Male, Mesh Length 0.61m (24.00")



Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

UL E61303

General

Product Family Cable Grips
Series [130096](#)
Eye Type N/A
NEMA Rating NEMA 4
O-Ring No
Overview [Strain-Relief Cord Grips](#)
Product Name Liquid-Tight
Type Strain Relief Grip
UPC 78678837106

Physical

Approximate Break Strength N/A
Bale Length N/A
Body Style Straight
Cable Diameter N/A
Color - Grommet N/A
Gender Male
Material - Body Malleable Iron, Zinc Plated Steel
Material - Grip Stainless Steel
Mesh Length 0.61m (24.00")
Net Weight 68.560/kg
Number of Holes N/A
Thread Size 2" NPT

Material Info

Engineering Number 37106

Reference - Drawing Numbers

Sales Drawing SD-130096-104

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130096](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300960079](#)