

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300970341](#)
Status: **Active**
Overview: [Strain-Relief Cord Grips](#)
Description: MAX-LOC Strain Relief Cord-Sealing Grip, 3/4" NPT, Straight Male, Cable Diameter 9.53-11.10mm (.375-.437"), Stainless Steel Mesh and Compression Nut

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

CSA LR32159

General

Product Family Cable Grips
Series [130097](#)
Eye Type N/A
NEMA Rating NEMA 3R
O-Ring No
Overview [Strain-Relief Cord Grips](#)
Product Name MAX-LOC
Type Strain Relief Grip
UPC 78678837137
Use With 3/4" NPT MAX-LOC Lock Nut [1300990144](#) , 3/4" NPT MAX-LOC Gasket Sealing Ring [1300990150](#) , 3/4" NPT MAX-LOC O-Ring [1301800333](#)

Physical


Approximate Break Strength N/A
Bale Length N/A
Body Style Straight
Cable Diameter 9.53-11.10mm (.375-.437")
Color - Grommet Green
Gender Male
Material - Body Stainless Steel
Material - Grip Stainless Steel
Mesh Length N/A
Number of Holes 1
Thread Size 3/4" NPT

Material Info

Engineering Number 5624MSS

Reference - Drawing Numbers

Sales Drawing SD-130097-102



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130097](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300970341](#)