

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300980090](#)
Status: **Active**
Overview: [Strain-Relief Cord Grips](#)
Description: MAX-LOC Strain Relief Cord-Sealing Grip, 1/2" NPT, 90° Angle Male with O-Ring, Cable Diameter 12.70-14.27mm (.500-.562")

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR32159
UL E76954

General

Product Family Cable Grips
Series [130098](#)
Eye Type N/A
NEMA Rating NEMA 6P
O-Ring Yes
Overview [Strain-Relief Cord Grips](#)
Product Name MAX-LOC
Type Strain Relief Grip
UPC 78678855332
Use With 1/2" NPT MAX-LOC Lock Nut [1300990143](#)

Physical

Approximate Break Strength N/A
Bale Length N/A
Body Style 90° Angle
Cable Diameter 12.70-14.27mm (.500-.562")
Color - Grommet N/A
Gender Male
Material - Body Nylon
Material - Grip N/A
Mesh Length N/A
Number of Holes 1
Thread Size 1/2" NPT

Material Info

Engineering Number 5533W



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130098](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300980090