

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300980427

Status:

Active

Overview:

Strain-Relief Cord Grips

Description:

MAX-LOC Strain Relief Cord-Sealing Grip, 1" NPT, 90° Angle Male with O-Ring, Cable Diameter 12.70-15.88mm (.500-.625")

Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR32159
UL	E76954
General	
Product Family	Cable Grips
Series	130098
Eye Type	N/A
NEMA Rating	NEMA 6P
O-Ring	Yes
Overview	Strain-Relief Cord Grips
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78172538420
Use With	MAX-LOC Lock Nut 1" NPT 1300990145
Physical	
Approximate Break Strength	N/A
Bale Length	N/A
Body Style	90° Angle
Cable Diameter	12.70-15.88mm (.500-.625")
Color - Grommet	Gray
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Net Weight	92.532/g
Number of Holes	1
Thread Size	1" NPT
Material Info	
Engineering Number	5549W



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130098 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1300980427](#)