

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301020138](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Super-Safeway Rubber Hand Lamp with 100W Open End Guard

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
UL E59251

General
Product Family Portable Lighting
Series [130102](#)
NEMA Configuration N/A
Outlet None
Overview [Hand Lamps](#)
Product Name Super-Safeway
Type Hand Lamps
UPC 78678860400

Physical
Cord Length - Primary N/A
Cord Length - Secondary N/A
Depth 153.92mm (6.060")
Duty Industrial
Guard Included Yes
Guard Type Open End
Height 311.66mm (12.270")
Length N/A
Material - Guard #8 Gauge Zinc-plated Steel
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical
Bulb Type Incandescent
Cord Type - Primary 16/3 SOOW
Lamp Type A21
Lamp Wattage - Maximum 100W
Lumens 1000
On/Off Switch No
Voltage (Fixture) - Maximum 240V

Material Info
Engineering Number 110



Series image - Reference only

<u>EU ELV</u> Not Reviewed	
<u>EU RoHS</u> Not Reviewed	<u>China RoHS</u>
<u>REACH SVHC</u> Not Reviewed	
<u>Halogen-Free</u> <u>Status</u> Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130102](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301020138