

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301020152

Status:

Active

Overview:

Hand Lamps

Description:

Super-Safeway Rubber Hand Lamp with 300W, Open End Vinyl Coated Guard, 15.24m (50.0') 16/3 SOOW

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR85374
General	
Product Family	Portable Lighting
Series	130102
NEMA Configuration	NEMA 5-15
Outlet	None
Overview	Hand Lamps
Product Name	Super-Safeway
Type	Hand Lamps
UPC	78678860507
Physical	
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Depth	190.50mm (7.500")
Duty	Industrial
Guard Included	Yes
Guard Type	Insulated, Open End
Height	371.35mm (14.620")
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Incandescent
Cord Type - Primary	16/3 SOOW
Lamp Type	A23
Lamp Wattage - Maximum	300W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	240V
Material Info	
Engineering Number	111IB163



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130102 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1301020152](#)