

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1301020233](#)  
**Status:** **Active**  
**Overview:** [Hand Lamps](#)  
**Description:** Super-Safeway Rubber Hand Lamp, PAR 38 Guard, with Switch, 15.24m (50.0') 16/3 SOOW

**Documents:**  
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

|                             |                            |
|-----------------------------|----------------------------|
| <b>Agency Certification</b> |                            |
| CSA                         | LR85374                    |
| <b>General</b>              |                            |
| Product Family              | Portable Lighting          |
| Series                      | <a href="#">130102</a>     |
| NEMA Configuration          | NEMA 5-15                  |
| Outlet                      | Side                       |
| Overview                    | <a href="#">Hand Lamps</a> |
| Product Name                | Super-Safeway              |
| Type                        | Hand Lamps                 |
| UPC                         | 78678835493                |
| <b>Physical</b>             |                            |
| Cord Length - Primary       | 15.24m (50.0')             |
| Cord Length - Secondary     | N/A                        |
| Depth                       | N/A                        |
| Duty                        | Industrial                 |
| Guard Included              | Yes                        |
| Guard Type                  | Open End, PAR 38           |
| Height                      | 285.50mm (11.240")         |
| Length                      | N/A                        |
| Material - Guard            | #8 Gauge Zinc-plated Steel |
| Mounting Style              | Hand Held                  |
| Packaging Type              | Carton                     |
| Socket Construction         | N/A                        |
| <b>Electrical</b>           |                            |
| Bulb Type                   | Incandescent               |
| Cord Type - Primary         | 16/3 SOOW                  |
| Lamp Type                   | PAR38                      |
| Lamp Wattage - Maximum      | 100W                       |
| Lumens                      | 1000                       |
| On/Off Switch               | Yes                        |
| Voltage (Fixture) - Maximum | 240V                       |
| <b>Material Info</b>        |                            |
| Engineering Number          | 119UB163                   |



Series image - Reference only

|                                                               |                   |
|---------------------------------------------------------------|-------------------|
| <b>EU ELV</b><br><b>Not Relevant</b>                          |                   |
| <b>EU RoHS</b><br><b>Not Reviewed</b>                         | <b>China RoHS</b> |
| <b>REACH SVHC</b><br>Not Reviewed                             |                   |
| <b>Halogen-Free</b><br><b>Status</b><br><b>Not Reviewed</b>   |                   |
| For more information, please visit <a href="#">Contact US</a> |                   |
| China ROHS                                                    | Not Reviewed      |
| ELV                                                           | Not Relevant      |
| RoHS Phthalates                                               | Not Reviewed      |

**Search Parts in this Series**  
[130102](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301020233