

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301020301

Status:

Active

Overview:

Hand Lamps

Description:

Safeway Phenolic Hand Lamp, with Switch, Cord Type 16/3 SJTOW, Cord Length 7.62m (25.0')



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Portable Lighting
Series	130102
NEMA Configuration	NEMA 5-15
Outlet	None
Overview	Hand Lamps
Product Name	Safety Yellow
Type	Hand Lamps
UPC	78678800995
Physical	
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Depth	6.045mm (2.380")
Duty	Commercial
Guard Included	No
Guard Type	N/A
Height	165.10mm (6.500")
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Incandescent
Cord Type - Primary	16/3 SJTOW
Lamp Type	A21
Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	240V
Material Info	
Engineering Number	42-4390

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130102 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301020301