

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301080157](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Super-Safeway Twin Tube 30W Fluorescent Work Light, Cord Type 16/3 SJOW Feed Thru 1.22m (4.0') Cord Length

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
UL	E174254
General	
Product Family	Portable Lighting
Series	130108
NEMA Configuration	NEMA 5-15
Outlet	Feed-Through
Overview	Wide-Area Lighting Products
Product Name	Super-Safeway
Type	Wide Area Lamps
UPC	78678867264
Physical	
Cord Length - Primary	1.22m (4.0')
Cord Length - Secondary	0.152m (6.00")
Depth	190.75mm (7.510")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	82.55mm (3.250")
Length	625.35mm (24.620")
Material - Globe	Butyrate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Adjustable Brackets
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Fluorescent
Cord Type - Primary	16/3 SJOW
Lamp Type	F15/T8
Lamp Wattage - Maximum	30W
Lumens	1820
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info	
Engineering Number	1335



EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130108](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301080157