

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301080179](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Watertite Wet Location 26W Fluorescent Hand Lamp with Switch, Cord Type 16/3 SJTOOW, Cord Length 7.62m (25.0')

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
Series [130108](#)
NEMA Configuration NEMA 5-15
NEMA Rating NEMA 4X
Outlet None
Overview [Wide-Area Lighting Products](#)
Product Name Watertite
Type Wide Area Lamps
UPC 78678830276

Physical

Cord Length - Primary 7.62m (25.0')
Cord Length - Secondary N/A
Depth 69.85mm (2.750")
Duty Wet Location
Guard Included No
Guard Type N/A
Height N/A
Length 444.50mm (17.500")
Material - Globe Butyrate
Material - Guard Nitrile Rubber 80 Shore A
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Fluorescent
Cord Type - Primary 16/3 SJTOOW
Lamp Type PL-C 26/41/4P
Lamp Wattage - Maximum 26W
Lumens 1800
On/Off Switch Yes
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 1926SA



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Relevant

Search Parts in this Series

[130108](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1301080179](#)