

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301100023](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Super-Safeway 1000W Halogen Floodlight, Stand Mount, with Guard, Cord Type 16/3 SOOW, Cord Length 7.62m (25.0')

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Portable Lighting
Series	130110
NEMA Configuration	NEMA 5-15
NEMA Rating	Rain Tight
Outlet	None
Overview	Wide-Area Lighting Products
Product Name	Super-Safeway
Type	Wide Area Lamps
UPC	78678885110

Physical

Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Depth	N/A
Duty	Industrial
Guard Included	Yes
Guard Type	Steel
Height	374.65mm (14.750")
Length	279.40mm (11.000")
Material - Globe	Tempered Glass
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Stand
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Quartz Halogen
Cord Type - Primary	16/3 SOOW
Lamp Type	T-3 RSC
Lamp Wattage - Maximum	1000W
Lumens	21000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info

Engineering Number	8511
--------------------	------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130110 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301100023