

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301120071](#)
Status: **Active**
Overview: [Lighting Accessories](#)
Description: Suptex Standard Socket Suptex Standard SOC



Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Portable Lighting
Series	130112
NEMA Configuration	N/A
Outlet	None
Overview	Lighting Accessories
Product Name	Woodhead
Type	Accessory
UPC	78678860891
Physical	
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	54.10mm (2.130")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	118.87mm (4.680")
Length	N/A
Material - Guard	N/A
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Incandescent
Lamp Type	A21
Lamp Wattage - Maximum	N/A
Lumens	N/A
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Engineering Number	1133

EU ELV Not Relevant	
EU RoHS Not Relevant	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130112](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301120071