

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301120246](#)
Status: **Active**
Overview: [Lighting Accessories](#)
Description: Guard Only (LITE-A-SITE), Polypropylene

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Portable Lighting
Series [130112](#)
NEMA Configuration N/A
Outlet None
Overview [Lighting Accessories](#)
Product Name Woodhead
Type Accessory
UPC 78678879982

Physical
Cord Length - Primary N/A
Cord Length - Secondary N/A
Depth 109.22mm (4.300")
Duty Commercial
Guard Included Yes
Guard Type Polypropylene
Height 165.10mm (6.500")
Length N/A
Material - Guard Polypropylene
Net Weight 45.359/g
Packaging Type Carton
Socket Construction N/A

Electrical
Bulb Type N/A
Lamp Type A21
Lamp Wattage - Maximum N/A
Lumens N/A
On/Off Switch No
Voltage (Fixture) - Maximum N/A

Material Info
Engineering Number STR101



Series image - Reference only

EU ELV
Not Reviewed

EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130112](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301120246 STR101