

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301140019](#)
Status: **Active**
Overview: [Lighting Accessories](#)
Description: Incandescent Stringlight Construction Guard 1-3/4 Neck Zinc Plated, Long, Narrow Profile

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Portable Lighting
Series	130114
NEMA Configuration	N/A
Outlet	N/A
Overview	Lighting Accessories
Product Name	Woodhead
Type	Accessory
UPC	78678861178
Physical	
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	120.65mm (4.750")
Duty	Industrial
Guard Included	Yes
Guard Type	Steel
Height	241.30mm (9.500")
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Net Weight	195.040/g
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	N/A
Lamp Type	PS30
Lamp Wattage - Maximum	N/A
On/Off Switch	N/A
Voltage (Fixture) - Maximum	N/A
Material Info	
Engineering Number	378



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130114](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301140019](#)