

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

[1301230080](#)

Status:

Active

Description:

I-Beam Festoon Intermediate Car Round S6

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Festoons
Series	130123
Cable Height - Maximum	26.16mm (1.030")
Combined Cable Weight-Max./Car	79.38kg (175.0 lb)
Component Type	Car - Intermediate
Depth	209.55mm (8.250")
Duty	Heavy
Height	336.55mm (13.250")
Length	325.88mm (12.830")
Product Name	Aero-Motive
Type	I-Beam
UPC	78678863097
Physical	
Beam Size	S6 - 152.40mm
Material - Coating	Powder Coating
Material - Metal	Steel
Material - Wheel	Polyurethane
Number of Cars	1
Packaging Type	Individual Carton
Saddle Radius	112.78mm (4.440")
Thread Size	N/A
Travel Speed - Maximum	121.92 mpm (400 fpm)
Wire/Cable Type	Round
Material Info	
Engineering Number	0639610

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130123](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301230080