

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301230115](#)
Status: **Active**
Description: I-Beam Festoon Intermediate Car 605 PR Steel Wheels



EU ELV Not Reviewed	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130123](#) Series

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Festoons
Series	130123
Cable Height - Maximum	19.05mm (.750")
Cable Width - Maximum	98.00mm (3.858")
Combined Cable Weight-Max./Car	158.76kg (350.0 lb)
Component Type	Car - Lead
Depth	137.92mm (5.430")
Duty	Heavy
Height	372.87mm (14.680")
Length	254.00mm (10.000")
Product Name	Aero-Motive
Type	I-Beam
UPC	78678862911
Physical	
Beam Size	Patented Rail 82.55mm
Material - Coating	Powder Coating
Material - Metal	Steel
Material - Wheel	Steel
Number of Cars	1
Packaging Type	Individual Carton
Saddle Radius	79.50mm (3.130")
Thread Size	N/A
Travel Speed - Maximum	121.92 mpm (400 fpm)
Wire/Cable Type	Flat
Material Info	
Engineering Number	S605131

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301230115