

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301230123

Status:

Active

Description:

I-Beam Festoon Intermediate Car 605 S6, for 6.0" I-Beam, Steel Wheels and Kick-up Wheels



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Festoons
Series	130123
Cable Height - Maximum	19.05mm (.750")
Cable Width - Maximum	98.00mm (3.858")
Combined Cable Weight-Max./Car	158.76kg (350.0 lb)
Component Type	Car - Intermediate
Depth	209.55mm (8.250")
Duty	Heavy
Height	282.00 (11.100")
Length	254.00mm (10.000")
Product Name	Aero-Motive
Type	I-Beam
UPC	78678862918
Physical	
Beam Size	S6 - 152.40mm
Material - Coating	Powder Coating
Material - Metal	Steel
Material - Wheel	Steel
Number of Cars	1
Packaging Type	Individual Carton
Saddle Radius	79.50mm (3.130")
Thread Size	N/A
Travel Speed - Maximum	121.92 mpm (400 fpm)
Wire/Cable Type	Flat
Material Info	
Engineering Number	S605611

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130123 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301230123