

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301280111

Status:

Active

Overview:

Description:

Woodhead FS Black Phenolic Resin Box, (2) 12.70mm (.500") Threaded Knock-out Openings

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Relevant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Agency Certification	
UL	E117594
General	
Product Family	Power Distribution
Series	130128
Enclosure Rating	N/A
GFCI Reset	N/A
Mounting Style	Permanent
Open Neutral Relay	N/A
Overview	outlet_boxes
Product Name	Woodhead
Receptacle Type	N/A
Type	FS Box - Industrial Duty
UPC	78678872450
Physical	
Cord Diameter	N/A
Cord Grip Body Size	N/A
Cord Length	N/A
Feed-Thru	No
Flip Lid	No
Material - Housing	N/A
Number of Receptacles	0
Packaging Type	Carton
Electrical	
Cord Type	N/A
Current - Maximum per Contact	N/A
GFCI	No
Ground Continuity Monitor	No
NEMA Configuration	N/A
Voltage - Maximum	N/A
Material Info	
Engineering Number	450

Search Parts in this Series

130128 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[130128-0111](#) [450](#)