

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301280118](#)
Status: **Active**
Overview: [Outlet Boxes](#)
Description: Woodhead FD Gray Glass-Filled Polyester Box, (2) 25.40mm (1.000") Threaded Knock-out Openings

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

CSA LR32159
UL E117594

General

Product Family Power Distribution
Series [130128](#)
Enclosure Rating N/A
GFCI Reset N/A
Mounting Style Permanent
Open Neutral Relay N/A
Overview [Outlet Boxes](#)
Product Name Woodhead
Receptacle Type N/A
Type FD Box - Industrial Duty
UPC 78678872454

Physical

Cord Diameter N/A
Cord Grip Body Size N/A
Cord Length N/A
Feed-Thru Yes
Flip Lid No
Material - Housing PBT Glass-Filled
Number of Receptacles 0
Packaging Type Carton

Electrical

Cord Type N/A
Current - Maximum per Contact N/A
GFCI No
Ground Continuity Monitor No
NEMA Configuration N/A
Voltage - Maximum N/A

Material Info

Engineering Number 454

Reference - Drawing Numbers

Sales Drawing 1301280113-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

China RoHS

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130128](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301280118