

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301280151

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Watertite Two-Gang FD PVC, Non-metallic Box, Yellow, 88.9mm (3.50") Depth, 67.3 Cubic Inch Capacity, 1" unthreaded conduit openings with reducers for 3/4" and 1/2" conduit



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E117594
General	
Product Family	Power Distribution
Series	130128
Enclosure Rating	NEMA 4X
GFCI Reset	N/A
Mounting Style	Permanent
Open Neutral Relay	N/A
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite
Receptacle Type	N/A
Type	FD Box - Industrial Duty
UPC	78172542281
Physical	
Cord Diameter	N/A
Cord Grip Body Size	N/A
Cord Length	N/A
Feed-Thru	No
Flip Lid	No
Material - Housing	PVC
Net Weight	1041.448/g
Number of Receptacles	0
Packaging Type	Carton
Electrical	
Cord Type	N/A
Current - Maximum per Contact	N/A
GFCI	No
Ground Continuity Monitor	No
NEMA Configuration	N/A
Voltage - Maximum	N/A
Material Info	
Engineering Number	455-FD2
Reference - Drawing Numbers	
Sales Drawing	SD-130128-002

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per -ED/01/2018 (15 January 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

130128 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301280151](#)