

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301280162](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Three-Gang FD PVC, Non-metallic Box, Black, 88.9mm (3.50") Depth, 109.1 Cubic Inch Capacity, 1" unthreaded conduit openings with reducers for 3/4" and 1/2" conduit

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E117594

General

Product Family Power Distribution
Series [130128](#)
Enclosure Rating NEMA 4X
GFCI Reset N/A
Mounting Style Permanent
Open Neutral Relay N/A
Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
Product Name Watertite
Receptacle Type N/A
Type FD Box - Industrial Duty
UPC 78172542285

Physical

Cord Diameter N/A
Cord Grip Body Size N/A
Cord Length N/A
Feed-Thru No
Flip Lid No
Material - Housing PVC
Net Weight 1543.119/g
Number of Receptacles 0
Packaging Type Carton

Electrical

Cord Type N/A
Current - Maximum per Contact N/A
GFCI No
Ground Continuity Monitor No
NEMA Configuration N/A
Voltage - Maximum N/A

Material Info

Engineering Number 455-FD3BLK

Reference - Drawing Numbers

Sales Drawing SD-130128-003



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per
-ED/01/2018 (15
January 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[130128](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301280162](#)