

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301350015](#)
Status: **Active**
Overview: [Outlet Boxes](#)
Description: Super-Safeway Angled GFCI Outlet Box, Feed-Thru, F3 (3/4") Cord Grip Body, Including NEMA 5-20 GFCI & Duplex Receptacles with Flip Lids and 1.83m (6.0') Cord Length, 12/3 SOOW Cord & Cont. Monitor

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Power Distribution
Series	130135
Enclosure Rating	NEMA 4
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	No
Overview	Outlet Boxes
Product Name	Super-Safeway
Receptacle Type	GFCI Duplex
Type	Angled GFCI Outlet Box
UPC	78678805138
Physical	
Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	1.83m (6.0')
Feed-Thru	Yes
Flip Lid	Yes
Material - Housing	Rubber
Number of Receptacles	2
Packaging Type	Carton
Electrical	
Cord Type	12/3 SOOW
Current - Maximum per Contact	20.0A
GFCI	Yes
Ground Continuity Monitor	Yes
NEMA Configuration	NEMA 5-20
Voltage - Maximum	120V
Material Info	
Engineering Number	3324FL123



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130135](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1301350015](#)