

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301360055

Status:

Active

Overview:

Outlet Boxes

Description:

Super-Safeway Multi-Tap (3) Non-NEMA 20A/125V/250V Outlet Box with Buss Bars, 7.62m (25.0') Cord Length, 14/3 SOW Cord, Non-NEMA 20A/125V/250V Plug

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
General	
Product Family	Power Distribution
Series	130136
Enclosure Rating	N/A
GFCI Reset	N/A
Mounting Style	Portable
Open Neutral Relay	N/A
Overview	Outlet Boxes
Product Name	Super-Safeway
Receptacle Type	Triple
Type	Multi-Tap and Strip Cordset
UPC	78678875659
Physical	
Cord Diameter	13.59mm (.535")
Cord Grip Body Size	Double C-Clamp
Cord Length	7.62m (25.0')
Feed-Thru	No
Flip Lid	No
Material - Housing	Rubber
Number of Receptacles	3
Packaging Type	Carton
Electrical	
Cord Type	14/3 SOOW
Current - Maximum per Contact	20.0A
GFCI	No
Ground Continuity Monitor	No
NEMA Configuration	Non-NEMA
Voltage - Maximum	120V
Material Info	
Engineering Number	32708A143



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130136 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301360055