

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301370090

Status:

Active

Overview:

Outlet Boxes

Description:

Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, NEMA 5-20 Duplex Receptacles, Cord Clamp, Duplex Cover Plates, 7.62m (25.0') Cord Length, 12/3 SOOW Cord, 5-20 Plug



Documents:	
Brochure (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
CSA	LR6837
UL	E38085
General	
Product Family	Power Distribution
Series	130137
Enclosure Rating	N/A
GFCI Reset	N/A
Mounting Style	Portable
Open Neutral Relay	N/A
Overview	Outlet Boxes
Product Name	Super-Safeway
Receptacle Type	Duplex
Type	Multiple Outlet Box
UPC	78678834771
Physical	
Cord Diameter	15.24mm (.600")
Cord Grip Body Size	Double C-Clamp
Cord Length	7.62m (25.0')
Feed-Thru	No
Flip Lid	No
Material - Housing	Rubber
Number of Receptacles	2
Packaging Type	Carton
Electrical	
Cord Type	12/3 SOOW
Current - Maximum per Contact	20.0A
GFCI	No
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-20
Voltage - Maximum	125V
Material Info	
Engineering Number	3000-10A123

EU ELV	
Not Relevant	
EU RoHS	
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130137 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301370090