

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301370092](#)
Status: **Active**
Overview: [Outlet Boxes](#)
Description: Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, NEMA 5-20 Duplex Receptacles, Cord Clamp, Duplex Cover Plates, 15.24m (50.0') Cord Length, 12/3 SOOW Cord, 5-20 Plug



Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	LR6837
UL	E38085

General

Product Family	Power Distribution
Series	130137
Enclosure Rating	N/A
GFCI Reset	N/A
Mounting Style	Portable
Open Neutral Relay	N/A
Overview	Outlet Boxes
Product Name	Super-Safeway
Receptacle Type	Duplex
Type	Multiple Outlet Box
UPC	78678837189

Physical

Cord Diameter	15.24mm (.600")
Cord Grip Body Size	Double C-Clamp
Cord Length	15.24m (50.0')
Feed-Thru	No
Flip Lid	No
Material - Housing	Rubber
Number of Receptacles	2
Packaging Type	Carton

Electrical

Cord Type	12/3 SOOW
Current - Maximum per Contact	20.0A
GFCI	No
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-20
Voltage - Maximum	125V

Material Info

Engineering Number	3000-10B123
--------------------	-------------

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130137](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301370092](#)