This document was generated on 03/05/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1301370093

Status: Active

Overview: Outlet Boxes

Description: Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, NEMA 5-20 Duplex Receptacles, Cord Clamp, Duplex Cover Plates, 0.305m (1.0') Cord Length, 12/3 SOOW Cord, 5-20 Plug

Series image - Reference only

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR6837
UL	E38085

General

Product Family	Power Distribution
Series	130137
Enclosure Rating	N/A
GFCI Reset	N/A
Mounting Style	Portable
Open Neutral Relay	N/A
Overview	Outlet Boxes
Product Name	Super-Safeway
Receptacle Type	Duplex
Type	Multiple Outlet Box
UPC	78678804508

Physical

Cord Diameter	15.24mm (.600")
Cord Grip Body Size	Double C-Clamp
Cord Length	0.305m (1.0')
Feed-Thru	No
Flip Lid	No
Material - Housing	Rubber
Number of Receptacles	2
Packaging Type	Carton

Electrical

Cord Type	12/3 SOOW
Current - Maximum per Contact	20.0A
GFCI	No
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-20
Voltage - Maximum	125V

Material Info

Engineering Number	3000-10E123

EU ELV
Not Reviewed

EU RoHS
Not Reviewed

China RoHS

REACH SVHC
Not Reviewed

Halogen-Free Status
Not Reviewed

For more information, please visit Contact US

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
130137 Series

This document was generated on 03/05/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:
1301370093