

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301370105](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, NEMA LNEMA 5-15 Duplex Receptacles, Cord Clamp, Duplex Cover Plates

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
UL E46237

General

Product Family Power Distribution
Series [130137](#)
Enclosure Rating N/A
GFCI Reset N/A
Mounting Style Portable
Open Neutral Relay N/A
Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
Product Name Super-Safeway
Receptacle Type Duplex
Type Multiple Outlet Box
UPC 78678874250

Physical

Cord Diameter 8.26-16.64mm (.325-.655")
Cord Grip Body Size Double C-Clamp
Cord Length N/A
Feed-Thru No
Flip Lid No
Material - Housing Rubber
Number of Receptacles 2
Packaging Type Carton

Electrical

Cord Type N/A
Current - Maximum per Contact 15.0A
GFCI No
Ground Continuity Monitor No
NEMA Configuration NEMA 5-15
Voltage - Maximum 125V

Material Info

Engineering Number 3000-2



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130137](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301370105