

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301370164

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Watertite Multiple Outlet Box, Extended Depth, (1) NEMA 5-20 Manual reset GFCI with Flip Lid, Open Neutral Relay, 1.83M (6.0') Cord Length, 12/3 SOOW Cord, 5-15 Plug

Documents:	
Brochure (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
General	
Product Family	Power Distribution
Series	130137
Enclosure Rating	N/A
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite
Receptacle Type	Duplex
Type	Multiple Outlet Box
UPC	78678874302
Physical	
Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	1.83m (6.0')
Feed-Thru	Yes
Flip Lid	Yes
Material - Housing	Rubber
Number of Receptacles	1
Packaging Type	Carton
Electrical	
Cord Type	12/3 SOOW
Current - Maximum per Contact	N/A
GFCI	Yes - Receptacle
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-20
Voltage - Maximum	125V
Material Info	
Engineering Number	3070W-GFI20



EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
130137 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301370164