

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301370180

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Super-Safeway Multiple Outlet Box, Extended Depth, 2-Sided, (1) NEMA 5-15 GFCI Receptacles with Flip Lid, Open Neutral Relay, Top-of-Box GCM, 0.91m 12/3 SOOW Cord on Both sides, 5-15 Plug & Conn



Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
General	
Product Family	Power Distribution
Series	130137
Enclosure Rating	NEMA 4
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Super-Safeway
Receptacle Type	GFCI Duplex
Type	Multiple Outlet Box
UPC	78678875162
Physical	
Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	1.83m (6.0')
Feed-Thru	No
Flip Lid	No
Material - Housing	Rubber
Number of Receptacles	1
Packaging Type	Carton
Electrical	
Cord Type	12/3 SOOW
Current - Maximum per Contact	15.0A
GFCI	Yes
Ground Continuity Monitor	Yes
NEMA Configuration	NEMA 5-15
Voltage - Maximum	125V
Material Info	
Engineering Number	3080-GFI

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130137 Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301370180](#)