

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301370196](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Super-Safeway Multiple Outlet Box, Extended Depth, 2-Sided, F2 (1/2") Cord Grip Body, with Flip Lids for (2),NEMA 5-20 Duplex Receptacles, 30.48m (100.0') Cord Length, 12/3 SOOW,NEMA 5-20 Plug

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
UL E38085

General

Product Family Power Distribution
Series [130137](#)
Enclosure Rating NEMA 4
GFCI Reset N/A
Mounting Style Portable
Open Neutral Relay N/A
Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
Product Name Super-Safeway
Receptacle Type Duplex
Type Multiple Outlet Box
UPC 78678875128

Physical

Cord Diameter 15.24mm (.600")
Cord Grip Body Size F2 1/2"
Cord Length 30.48m (100.0')
Feed-Thru No
Flip Lid Yes
Material - Housing Rubber
Number of Receptacles 2
Packaging Type Carton

Electrical

Cord Type 12/3 SOOW
Current - Maximum per Contact 20.0A
GFCI No
Ground Continuity Monitor No
NEMA Configuration NEMA 5-20
Voltage - Maximum 250V

Material Info

Engineering Number 3085-10D123



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130137](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301370196](#)