

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301370236](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite GFCI Multiple Outlet FD Box, (1)NEMA 5-20 Duplex with Flip Lids, 30.48m (100.0') Cord Length 14/3 SOOW Cord, NEMA 5-20 Watertite Plug

Documents:
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Power Distribution
Series	130137
Enclosure Rating	NEMA 4X
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	No
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite
Receptacle Type	Duplex
Type	GFCI Multiple Outlet Box
UPC	78678828307
Physical	
Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	30.48m (100.0')
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Nylon
Number of Receptacles	1
Packaging Type	Carton
Electrical	
Cord Type	12/3 SOOW
Current - Maximum per Contact	20.0A
GFCI	Yes
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-20
Voltage - Maximum	120V
Material Info	
Engineering Number	3304GFD123



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130137](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301370236