

E

D

C

B

A

E

D

C

B

A

6

5

4

3

2

1

SUPPORT GRIP
STANDARD DUTY
DOUBLE EYE
PART NO. 35002

WIRE MESH
TINNED PHOSPHOR
BRONZE

#12-3 SOW CORD
CORD LENGTH: SEE TABLE
COLOR: YELLOW

FLIP COVER
POLYCARBONATE
COLOR: YELLOW

TWO NEMA 5-20
DUPLEX RECEPTACLE
COLOR: BROWN

COVER PLATE
NYLON
COLOR: YELLOW

CRIMP CONNECTOR
ALUMINUM

FERRULE
ALUMINUM

BALE WIRE
STAINLESS STEEL

COMPRESSION NUT
NYLON
COLOR: YELLOW

RUBBER OUTLET
BOX
COLOR: YELLOW

RUBBER
HUSK
COLOR:
YELLOW

NEMA L5-20
SUPER-SAFEWAY
PART NO. 2647
COLOR: YELLOW

NYLON
CLAMP
COLOR: YELLOW

SHOULDER PROTECTOR
ALUMINUM

FRICTION RING
HIGH-DENSITY POLYETHELENE

GROMMET
NITRILE PVC

CORD GRIP
NYLON
COLOR: YELLOW

LOCKNUT
STEEL

5.37/136
REF.

3.91/99
REF.

2.50/64
REF.

17.0/432
REF.

15/381
REF.

4.38/111
REF.

MATERIAL NO.	ENGINEERING NO.	CORD LENGTH
1301370299	130137-0299	6 FEET
1301370302	130137-0302	8 FEET

ADDED 130137-0302	11/19/13
EC NO: IGC2013-0392	DRWN: HRUIZ01
CHKD: HKNEELAN	APPR: JFMURPHY
2013/08/10	
REV	DESCRIPTION
B	

QUALITY SYMBOLS
$\nabla=0$
$\nabla C=0$

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	$\pm .---$	$\pm .---$
3 PLACES	$\pm .---$	$\pm .005$
2 PLACES	$\pm .13$	$\pm .010$
1 PLACE	$\pm .25$	$\pm .020$
ANGULAR $\pm 5^\circ$		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE INCH/MM	
DRAWN BY	DATE
HRUIZ01	2013/07/22
CHECKED BY	DATE
HKNEELAN	2013/07/22
APPROVED BY	DATE
JFMURPHY	2013/08/10
MATERIAL NO.	
SEE TABLE	
SIZE	
A	

SCALE NTS	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION
TITLE		
MULTIPLE OUTLET BOX #12-3 SOW CORD 2647 PLUG AND 35002 GRIP		
 MOLEX INCORPORATED		
DOCUMENT NO. SD-130137-037		SHEET NO. 1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301370302](#)