

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301430115

Status:

Active

Overview:

Heavy-Duty Industrial Wiring Devices

Description:

Super-Safeway Cordset 14 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 7.62m (25.0'), NEMA 6-20, 250V

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR6837

UL

E38085

General

Product Family

Wiring Devices

Series

130143

IP Rating

N/A

NEMA Configuration

NEMA 6-20

Overview

Heavy-Duty Industrial Wiring Devices

Product Name

Super-Safeway

Receptacle Type

Single

Specialty

N/A

Type

Cordset

UPC

78678870161

Physical

Flange

No

Flip Lid

No

Gender

Male-Female

Length

7.62m (25.0')

Locking Blade

No

Net Weight

199.000/kg

Poles

2-pole/3-wire

Electrical

Cord Type

14/3 SOOW

Current - Maximum per Contact

20.0A

GFCI

No

Lighted Connector

No

Voltage - Maximum

250V

Material Info

Engineering Number

1448A143



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130143 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301430115