

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301430139

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Watertite Cordset 12 Gauge SJOW, 2 Pole/3 Wire, Cordset Length 15.24m (50.0'), NEMA 5-15, 125V, Inline GFCI

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR6837

UL

E38085

General

Product Family

Wiring Devices

Series

130143

IP Rating

IP67

NEMA Configuration

NEMA 5-15

Overview

Watertite Extreme Wet-Location Wiring Solutions

Product Name

Watertite

Receptacle Type

Single

Specialty

N/A

Type

Cordset

UPC

78678822528

Physical

Cord Grip Body Size

F2 1/2"

Flange

No

Flip Lid

No

Gender

Male-Female

Length

15.24m (50.0')

Locking Blade

No

Net Weight

777.000/kg

Poles

2-pole/3-wire

Electrical

Cord Type

12/3 SJOW

Current - Maximum per Contact

15.0A

GFCI

Yes-In-line

Lighted Connector

No

Voltage - Maximum

125V

Material Info

Engineering Number

14W47B123IN



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130143 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301430139