

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301430140

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Watertite Extreme Cordset 14 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 15.24m (50.0'), NEMA 5-15, 125V



Series image - Reference only

Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Brochure \(PDF\)](#)

Agency Certification	
CSA	LR6837
UL	E38085
General	
Product Family	Wiring Devices
Series	130143
IP Rating	IP67
NEMA Configuration	NEMA 5-15
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Receptacle Type	Single
Specialty	N/A
Type	Cordset
UPC	78678879656
Physical	
Cord Grip Body Size	F2 1/2"
Flange	No
Flip Lid	No
Gender	Male-Female
Length	15.24m (50.0')
Locking Blade	No
Net Weight	777.000/g
Poles	2-pole/3-wire
Electrical	
Cord Type	14/3 SOOW
Current - Maximum per Contact	15.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V
Material Info	
Engineering Number	14W47B143
Reference - Drawing Numbers	
Sales Drawing	1301430140-000

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130143 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301430140