

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301430149

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Watertite Extreme Cordset 12 Gauge SJOW, 2 Pole/3 Wire, Cordset Length 30.48m (100.0'), NEMA 5-15, 125V, Inline GFCI

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR6837
UL		E38085
General		
Product Family		Wiring Devices
Series		130143
IP Rating		IP67
NEMA Configuration		NEMA 5-15
Overview		Watertite Extreme Wet-Location Wiring Solutions
Product Name		Watertite Extreme
Receptacle Type		Single
Specialty		N/A
Type		Cordset
UPC		78678822530
Physical		
Cord Grip Body Size		F2 1/2"
Flange		No
Flip Lid		No
Gender		Male-Female
Length		30.48m (100.0')
Locking Blade		No
Net Weight		999.000/kg
Poles		2-pole/3-wire
Electrical		
Cord Type		12/3 SJOW
Current - Maximum per Contact		15.0A
GFCI		Yes-In-line
Lighted Connector		No
Voltage - Maximum		125V
Material Info		
Engineering Number		14W47D123IN



EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130143 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301430149